





Designed for plunging

- Robust, patented geometry especially designed for plunging
- Equipped with 1610 grade that is optimized for plunging in HRSA
- Features coolant grooves on the shank for safe chip evacuation
- Offers excellent bending control

High productivity in tough materials

- Unique solution, optimal for high productivity in components with hidden slots, e.g. close blisk slots
- Extremely good productivity, as plunging allows for large cutting depth in limited time
- · Optimized for self-stabilizing effect, as the forces are directed in the axial direction
- Balanced front geometry with a_e = 30%×D_C
- Possible to machine with long overhangs

Blisk Roughing with plunge milling

Plunge milling is one of the preferred method when machining deep cavities.

Main Benefits:

- Axial feed movement directs cutting forces into the spindle to avoid vibrations, even when machining with long tools
- Extremely long overhangs, up to 6×D, can be used
- Suitable for complex shapes and limited space between blades





Solid end mill offer for HRSA roughing

Plunge milling





CoroMill® Plura Gannet 1610

Slot and shoulder milling





VFD 1725

Trochoidal milling





CoroMill® Plura HFS 1710

High speed milling







CoroMill® Plura Ceramic 6060

The Standard offer

Family	Dc range	Re/CHW	LU	Shank	No. of flutes	Coolant Grooves	Grade
2P070-PB	4–16 mm	CHW	4xDc	Weldon	4	Yes	1610
2P070-PB (inch)	0.188-0.625 inch	CHW	4xDc	Weldon	4	Yes	1610
2P090-PB	4–16 mm	CHW	6xDc	Weldon	4	Yes	1610

Standard Assortment and Tailor Made are made the same

Thanks to Design Automation, using 3D model automatic generation, Standard and Tailor Made, are now following the same process for design and manufacturing.



Tailor Made offer means:

- No engineering time
- Instantaneous turnaround of design and quotation
- Reconditioning quote included
- · Same Sandvik Coromant quality
- Consistent and secure delivery established with the quotation



Performance

Component: Blis

Material: Inconel 718

Operation:Slots between bladesMachine:STARRAG LX021

60%
Cycle time reduction
+800%
Tool life

	Competitor	Sandvik Coromant
Tool	Tool with Dc= 3mm	2P070-0400-PB 1610
Method	Trochoidal	Plunging
$\overline{z_n}$	4	4
n, rpm	2650	1990
v _c , m/min (ft/min)	25	25
v _f , mm/min (in/min)	160	96
f_z , mm/z (in/z)	0.015	0.012
a _p , mm (inch)		0.9
a _e , mm (inch)	0.2	4
Cycle time, min	90	36
Tool life, pcs	1/3 pcs - 5 blades , total 3 cutters	1 pcs - 15 blades, with 1 cutter

For more information, contact your local Sandvik Coromant representative or visit

Valuable services

Reconditioning



Reconditioning service is available.

Head office: AB Sandvik Coromant SE-811 81 Sandviken, Sweden E-mail: info.coromant@sandvik.com www.sandvik.coromant.com

C-1040:273 en-GB © AB Sandvik Coromant 2020



